



HALF-WAVE RECTIFIER TUBE

TANTALUM ANODE AND XENON GAS FILLING



BOTTOM VIEW
OF BASE

Maximum Rated Anode Current		
D-c. Meter Value-Continuous		6.4 amps
D-c. Meter Value-Overload less than 10 sec.		12.8 amps
Averaging Time		7 secs
Oscillograph Peak-Continuously recurring		40 amps
Max. Instantaneous Short Circuit Current (0.1sec.)		770 amps
Peak Inverse Voltage (Max. Instantaneous)		920 volts
Max. Commutation Factor (V/usec x A/usec)		0.66
Filament		
Voltage		2.5 volts
Current		21±2 amps
Heating Time (minimum)		60 secs
Average Arc Drop		
Average Tube		9 volts
Highest Tube at end of life		12 volts
Anode Starting Voltage (Instantaneous)		
Average Tube		12 volts
Highest Tube		30 volts
Ambient Temperature Limits		-55° to +75° C
Overall Dimensions		2-1/32" x 8-1/4" Max.
Weight		7 ozs.
Connections		
Filament		5-1/8" flexible leads with lugs for #10 studs
Anode		C1-5 cap (0.56" dia.) with ceramic insulator
		Vertical panel-mounted on two 1/4" studs 4-1/8" apart on a horizontal line.

The filament must be lit before drawing d-c. load current.

The anode is designed to operate at red heat when under full load.

All of the above values are for returns to the filament transformer center tap. Filament lead F- should be negative with respect to F+ during the anode conduction period.

The Engineering Manual contains additional information which should be considered in the circuit design.

ELECTRONS, INCORPORATED
127 Sussex Avenue
Newark 3, New Jersey