

EASTMAN Fine Grain Duplicating Panchromatic Negative Film 2234, 3234, 5234, 7234



EASTMAN Fine Grain Duplicating Panchromatic Negative Film 5234/7234 and EASTMAN Fine Grain Duplicating Panchromatic Negative Film 2234/3234, ESTAR Base, are characterized by very high sharpness. They have panchromatic sensitivity. These low-speed, black-and-white films are designed for making duplicate negatives from master positives, or internegatives from reversal originals. When used with EASTMAN Fine Grain Duplicating Positive Film 5366/7366, they produce negatives nearly equal to the original negative in tone rendering and printing detail.

BASE

5234/7234 Film has a gray acetate safety base. The back side of the base contains an anti-static layer with a carnauba wax lubricant.

2234/3234 Film has a gray ESTAR (polyester) base. The backside of the base contains a process-surviving anti-static layer.

DARKROOM RECOMMENDATIONS

Use a KODAK No. 3 Safelight Filter / dark green, with a 15-watt bulb, no closer to the film than 1.2 metres (4 feet).

STORAGE

Store unexposed film at 13°C (55°F) or lower. For extended storage, store at -18°C (0°F) or lower. Process exposed film promptly. Store processed film according to the recommendations in ANSI/PIMA IT9.11-1998: for medium-term storage (minimum of ten years), store at 25°C (77°F) or lower at a relative humidity of 20 to 50 percent; for extended-term storage (for preservation of material having permanent value), store at 21°C (70°F) or lower at a relative humidity of 20 to 30 percent. For active use, store at 25°C (77°F) or lower, at a relative humidity of 50 +/- 5 percent. This relates to optimized film handling rather than preservation; static, dust-attraction and curl-related problems are generally minimized at the higher relative humidity. After usage, the film should be returned to the appropriate medium- or long-term storage conditions as soon as possible.

For more information about medium- and long-term storage, see ANSI/PIMA IT9.11-1998, SMPTE RP131-1998, and KODAK Publications No. H-1, *KODAK Motion Picture Film*, and No. H-23, *The Book of Film Care*.

PROCESSING

The following process recommendations should be used as starting points for most conventional continuous-immersion processors with solutions prepared according to the formulas in KODAK Publication No.H-24.15, *Manual for Processing KODAK Motion Picture Films, Module 15*. The processing times may require modification for a particular machine.

Note: Observe precautionary information on product labels and on the Material Safety Data Sheets.

Processing Step	Temperature	Time	Replenishment Rate (mL per 100 ft)	
			35 mm	16 mm
KODAK Developer D-96 ¹	70 +/-1/2 F (21 +/-0.3 C)	- ²	1250 (D-96R)	625 (D-96R)
Stop Rinse ³	70 +/-2 F (21 +/-1 C)	50 sec	12,000	6000
KODAK Fixing Bath F-5 ¹	70 +/-2 F (21 +/-1 C)	6 min	850	425
Wash (counter-current)	70 +/-2 F (21 +/-1 C)	10 min	12,000	6000
Dry	95 F (35 C)	- ⁴		

¹ Agitation in the developer and fixing bath should be by recirculation through submerged spray jets that impinge on the film strands.

² Develop to recommended control gamma.

³ Countercurrent flow of fixer-laden water overflow from the wash tank, pH about 6.

⁴ Many factors affect the drying: air temperature, relative humidity (RH); volume, rate and distribution of the air flow; final squeegeeing, etc.

In a conventional convection-type drying cabinet with air at about 95°F (35°C) and 40 to 50 percent RH, drying will take 15 to 20 minutes. With an impingement-type drying cabinet, however, with a higher temperature and lower RH, drying time is greatly reduced. With either type of dryer, the film should be dry without tackiness 1/2 to 2/3 of the way through. Upon cooling to room temperature after leaving the dryer, the film should be in equilibrium with the room air at approximately 50 percent RH.

IDENTIFICATION

After processing, the product code numbers 2234, 3234, 5234, or 7234; emulsion and roll identification; and KEYCODE number (KD) are visible along the length of the film.

IMAGE STRUCTURE

MTF

The modulation-transfer curves, the diffuse rms granularity, and the resolving-power data were generated from samples of 5234 Film exposed with tungsten light and processed as recommended in Process D-96 at 70°F (21°C) to the recommended control gamma. For more information on image-structure characteristics, see KODAK Publication No. H-1, *KODAK Motion Picture Film*.

rms Granularity

Refer to curve.

Read with a microdensitometer using a 48-micrometer aperture.


The “perception” of the graininess of any film is highly dependent on scene content, complexity, color, and density. Other factors, such as film age, processing, exposure conditions, and telecine transfer may also have significant effects.

AVAILABLE ROLL LENGTHS


For information on film roll lengths, check *KODAK Motion Picture Film Price Catalog* or see a Kodak sales representative in your country.

CURVES


Characteristic Curves



Spectral Sensitivity Curves



Modulation Transfer Curve



NOTICE: The sensitometric curves and data in this publication represent product tested under the conditions of exposure and processing specified. They are representative of production coatings, and therefore do not apply directly to a particular box or roll of photographic material. They do not represent standards or specifications that must be met by Eastman Kodak Company. The company reserves the right to change and improve product characteristics at any time.

MORE INFORMATION

Outside the United States and Canada, please contact your Kodak representative.

You can also visit our web site at www.kodak.com/go/motion for further information. You may want to bookmark our location so you can find us easily the next time.

Films	<i>Cinematographer's Field Guide</i> KODAK Publication No. H-2
Image Structure	<i>KODAK Motion Picture Film</i> KODAK Publication No. H-1
Specification Numbers	<i>Cinematographer's Field Guide</i> KODAK Publication No. H-2
Storage	<i>KODAK Motion Picture Film</i> KODAK Publication No. H-1 <i>The Book of Film Care</i> KODAK Publication No. H-23
LAD	<i>LAD—Laboratory Aim Density</i> KODAK Publication No. H-61
Transfer	<i>KODAK Telecine Analysis Film User's Guide</i> KODAK Publication No. H-822 <i>KODAK Telecine Exposure Calibration Film User's Guide</i> KODAK Publication No. H-807

EASTMAN Fine Grain Duplicating Panchromatic Negative Film 2234, 3234, 5234, 7234

Kodak Locations

FOR DIRECT ORDERING IN THE UNITED STATES
AND CANADA: **1-800-621-FILM**

CHICAGO, ILLINOIS

Information: 630-910-4929

DALLAS, TEXAS

Information: 972-346-2979

HOLLYWOOD, CALIFORNIA

6700 Santa Monica Boulevard
Los Angeles, California
90038-1203

Information: 323-464-6131

NEW YORK, NEW YORK

360 West 31st Street
New York, New York
10001-2727

Information: 212-631-3418

LATIN AMERICA REGION

8600 NW 17th Street
Suite 200
Miami, Florida 33126-1006
Phone: 305-507-5146

CANADA

Kodak Canada Inc.
3500 Eglinton Avenue West
Toronto, Ontario
Canada M6M 1V3
Tel: 416-761-4922
Orders: 1-800-621-FILM (3456)
Fax: 416-761-4948
Toll Free Fax:
1-866-211-6311

Kodak Canada, Inc.
4 Place du Commerce, Suite 100
Ile des Soeurs
Verdun, Quebec
Canada H3E 1J4
Information: 514-761-7001
Fax: 514-768-1563
Orders: 1-800-621-FILM (3456)
Fax Orders: 1-866-211-6311

Kodak Canada, Inc.
4185 Still Creek Drive
Suite C150
Burnaby, British Columbia
Canada V5C 6G9
Tel: 1-800-621-FILM (3456)
Fax: 1-866-211-6311

EUROPEAN, AFRICAN, AND MIDDLE EASTERN REGION

Entertainment Imaging A2N
Kodak Ltd. Kodak House
P.O. Box 66, Station Road
Hemel Hempstead
Herts, HP1 1JU England
Local: +44-1442-844106
Fax: +44-1442-844072

Eastman Kodak SA
29-31 Route de L'Aeroport
Le Grand Sacconex, 1215
Case Postale 271
1215 Geneva 15
Switzerland
Information: +41-22-747-2000
Fax: +41-22-747-2200

GREATER ASIA & JAPAN REGION

AUSTRALIA
Kodak (Australasia) Pty. Ltd.
173 Elizabeth Street
Coburg, Victoria
Australia 3058
Phone: 61 3 8371 8520
Fax: 61 3 9353 2962

CHINA (Peoples Republic)

Beijing: 8610-6561-6561
Shanghai: 8621-6350-0888
Guangzhou: 8620-8319-8888

HONG KONG

Phone: 852-2564-9352

INDIA

Phone: 91-22-652-6826

INDONESIA

Phone: 62-21-570-5212

JAPAN

Phone: 813-5540-2280

KOREA

Phone: 82-2-708-5561

MALAYSIA

Phone: 603-7957-2722

NEW ZEALAND

Phone: 64-9-302-8665

PAKISTAN

Phone: 92-21-561-0150

PHILIPPINES

Phone: 632-810-0331

SINGAPORE

Phone: 65-6371-3388

TAIWAN

Phone: 886-2-2893-8108

THAILAND

Phone: 66-2-271-3040 Ext. 310

