

# MOSFET – Power, Single N-Channel

### 40 V, 12 mΩ, 35 A

## NVMYS011N04C

#### **Features**

- Small Footprint (5x6 mm) for Compact Design
- Low R<sub>DS(on)</sub> to Minimize Conduction Losses
- Low Q<sub>G</sub> and Capacitance to Minimize Driver Losses
- LFPAK4 Package, Industry Standard
- AEC-Q101 Qualified and PPAP Capable
- These Devices are Pb-Free and are RoHS Compliant

#### MAXIMUM RATINGS (T<sub>J</sub> = 25°C unless otherwise noted)

| Symbol                            | Parameter   |                     |                            | Value           | Unit |
|-----------------------------------|---|---------------------|----------------------------|-----------------|------|
| V <sub>DSS</sub>                  | Drain-to-Source Voltag  | е                   |                            | 40              | V    |
| V <sub>GS</sub>                   | Gate-to-Source Voltage  | Э                   |                            | ±20             | V    |
| I <sub>D</sub>                    | Continuous Drain<br>Current R <sub>BJC</sub>  | Steady<br>State     | T <sub>C</sub> = 25°C      | 35              | Α    |
|                                   | (Notes 1, 2, 3)   | State               | T <sub>C</sub> = 100°C     | 20              |      |
| P <sub>D</sub>                    | Power Dissipation   |                     | T <sub>C</sub> = 25°C      | 28              | W    |
|                                   | R <sub>θJC</sub> (Notes 1, 2)   |                     | T <sub>C</sub> = 100°C     | 9.1             |      |
| I <sub>D</sub>                    | Continuous Drain  | Steady<br>State     | T <sub>A</sub> = 25°C      | 13              | Α    |
|                                   | Current R <sub>0JA</sub> (Notes 1, 2, 3)  | State               | T <sub>A</sub> = 100°C     | 9.1             |      |
| P <sub>D</sub>                    | Power Dissipation   |                     |                            |                 | W    |
|                                   | R <sub>θJA</sub> (Notes 1, 2)   |                     | T <sub>A</sub> = 100°C     | 1.9             |      |
| I <sub>DM</sub>                   | Pulsed Drain Current  | T <sub>A</sub> = 25 | °C, t <sub>p</sub> = 10 μs | 173             | Α    |
| T <sub>J</sub> , T <sub>stg</sub> | Operating Junction and Storage Temperature  |                     |                            | -55 to<br>+ 175 | ç    |
| I <sub>S</sub>                    | Source Current (Body Diode)   |                     |                            | 24              | Α    |
| E <sub>AS</sub>                   | Single Pulse Drain-to-Source Avalanche Energy ( $T_J = 25$ °C, $I_{L(pk)} = 1.9$ A) |                     |                            | 75              | mJ   |
| TL                                | Lead Temperature for Soldering Purposes (1/8" from case for 10 s)                   |                     |                            | 260             | °C   |

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

#### THERMAL RESISTANCE MAXIMUM RATINGS


| Symbol          | Parameter  | Value | Unit |
|-----------------|--|-------|------|
| $R_{\theta JC}$ | Junction-to-Case - Steady State                              |       | °C/W |
| $R_{\theta JA}$ | R <sub>0JA</sub> Junction-to-Ambient - Steady State (Note 2) |       |      |

- The entire application environment impacts the thermal resistance values shown, they are not constants and are only valid for the particular conditions noted.
- 2. Surface-mounted on FR4 board using a 650 mm<sup>2</sup>, 2 oz. Cu pad.
- 3. Maximum current for pulses as long as 1 second is higher but is dependent on pulse duration and duty cycle.

| V <sub>(BR)DSS</sub> | R <sub>DS(ON)</sub> MAX | I <sub>D</sub> MAX |  |
|----------------------|-------------------------|--------------------|--|
| 40 V                 | 12 mΩ @ 10 V            | 35 A               |  |



LFPAK4 CASE 760AB



**N-CHANNEL MOSFET** 

#### **MARKING DIAGRAM**



011N04C = Specific Device Code A = Assembly Location

WL = Wafer Lot
 Y = Year
 W = Work Week

#### **ORDERING INFORMATION**

See detailed ordering, marking and shipping information on page 5 of this data sheet.

#### **ELECTRICAL CHARACTERISTICS** (T<sub>J</sub> = 25°C unless otherwise specified)


| Symbol                              | Parameter  | Test Condition  |                            | Min | Тур  | Max | Unit  |
|-------------------------------------|--|---|----------------------------|-----|------|-----|-------|
| OFF CHAR                            | ACTERISTICS  |   |                            |     |      |     |       |
| V <sub>(BR)DSS</sub>                | Drain-to-Source Breakdown Voltage                            | $V_{GS} = 0 \text{ V}, I_D = 250 \mu\text{A}$                         |                            | 40  |      |     | V     |
| V <sub>(BR)DSS</sub> /              | Drain-to-Source Breakdown Voltage<br>Temperature Coefficient |   |                            |     | 25   |     | mV/°C |
| I <sub>DSS</sub>                    | Zero Gate Voltage Drain Current                              | V <sub>GS</sub> = 0 V,  | T <sub>J</sub> = 25°C      |     |      | 10  |       |
|                                     |  | $V_{GS} = 0 V$ ,<br>$V_{DS} = 40 V$                                   | T <sub>J</sub> = 125°C     |     |      | 250 | μΑ    |
| I <sub>GSS</sub>                    | Gate-to-Source Leakage Current                               | $V_{DS} = 0 V, V_{GS}$  | = 20 V                     |     |      | 100 | nA    |
| ON CHARA                            | CTERISTICS (Note 4)  |   |                            |     |      |     |       |
| V <sub>GS(TH)</sub>                 | Gate Threshold Voltage                                       | $V_{GS} = V_{DS}, I_D$  | = 20 μΑ                    | 2.5 |      | 3.5 | V     |
| V <sub>GS(TH)</sub> /T <sub>J</sub> | Negative Threshold Temperature Coefficient                   |   |                            |     | -7.6 |     | mV/°C |
| R <sub>DS(on)</sub>                 | Drain-to-Source On Resistance                                | V <sub>GS</sub> = 10 V  | I <sub>D</sub> = 10 A      |     | 10   | 12  | mΩ    |
| 9FS                                 | Forward Transconductance                                     | V <sub>DS</sub> = 15 V, I <sub>D</sub>                                | = 10 A                     |     | 111  |     | S     |
| CHARGES,                            | CAPACITANCES & GATE RESISTANCE                               |   |                            |     |      |     | •     |
| C <sub>ISS</sub>                    | Input Capacitance  |   |                            |     | 420  |     |       |
| C <sub>OSS</sub>                    | Output Capacitance   | V <sub>GS</sub> = 0 V, f = 1 MHz                                      | z, V <sub>DS</sub> = 25 V  |     | 230  |     | pF    |
| C <sub>RSS</sub>                    | Reverse Transfer Capacitance                                 |   |                            |     | 11   |     |       |
| Q <sub>G(TOT)</sub>                 | Total Gate Charge  |   |                            |     | 7.9  |     | nC    |
| Q <sub>G(TH)</sub>                  | Threshold Gate Charge  |   |                            |     | 1.6  |     |       |
| Q <sub>GS</sub>                     | Gate-to-Source Charge  | V <sub>GS</sub> = 10 V, V <sub>DS</sub> = 3                           | 2 V; I <sub>D</sub> = 10 A |     | 2.5  |     |       |
| Q <sub>GD</sub>                     | Gate-to-Drain Charge   |   |                            |     | 1.5  |     |       |
| V <sub>GP</sub>                     | Plateau Voltage  |   |                            |     | 4.7  |     | V     |
| SWITCHING                           | CHARACTERISTICS (Note 5)                                     |   |                            |     |      |     |       |
| t <sub>d(ON)</sub>                  | Turn-On Delay Time   |   |                            |     | 8.0  |     |       |
| t <sub>r</sub>                      | Rise Time  | Vcc = 10 V Vc   | s = 32 V                   |     | 16   |     | 1     |
| t <sub>d(OFF)</sub>                 | Turn-Off Delay Time  | $V_{GS}$ = 10 V, $V_{DS}$ = 32 V,<br>$I_D$ = 10 A, $R_G$ = 1 $\Omega$ |                            |     | 16   |     | ns    |
| t <sub>f</sub>                      | Fall Time  |   |                            |     | 5.0  |     | 1     |
| DRAIN-SO                            | JRCE DIODE CHARACTERISTICS                                   |   |                            |     |      |     |       |
| V <sub>SD</sub>                     | Forward Diode Voltage  | $V_{GS} = 0 V$ , $T_J = 25^{\circ}C$                                  |                            |     | 0.84 | 1.2 |       |
|                                     |  | $I_S = 10 \text{ A}$  | T <sub>J</sub> = 125°C     |     | 0.71 |     | V     |
| t <sub>RR</sub>                     | Reverse Recovery Time  | $V_{GS}$ = 0 V, dIS/dt = 100 A/ $\mu$ s, I <sub>S</sub> = 10 A        |                            |     | 19   |     |       |
| t <sub>a</sub>                      | Charge Time  |   |                            |     | 9.0  |     | ns    |
| t <sub>b</sub>                      | Discharge Time   |   |                            |     | 10   |     | 1     |
| Q <sub>RR</sub>                     | Reverse Recovery Charge                                      |   |                            |     | 6.7  |     | nC    |

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

4. Pulse Test: pulse width  $\leq 300~\mu s$ , duty cycle  $\leq 2\%$ .

5. Switching characteristics are independent of operating junction temperatures.

#### **TYPICAL CHARACTERISTICS**



#### TYPICAL CHARACTERISTICS (continued)




Figure 7. Capacitance Variation




Figure 8. Gate-to-Source Voltage vs. Total Charge




Figure 9. Resistive Switching Time Variation vs. Gate Resistance




Figure 10. Diode Forward Voltage vs. Current




Figure 11. Maximum Rated Forward Biased Safe Operating Area




Figure 12. Maximum Drain Current vs. Time in Avalanche

#### TYPICAL CHARACTERISTICS (continued)




Figure 13. Thermal Characteristics

#### **DEVICE ORDERING INFORMATION**

| Device          | Marking | Package             | Shipping <sup>†</sup> |
|-----------------|---------|---------------------|-----------------------|
| NVMYS011N04CTWG | 011N04C | LFPAK4<br>(Pb-Free) | 3,000 / Tape & Reel   |

<sup>†</sup>For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, <u>BRD8011/D</u>.





### LFPAK4 4.90x4.15x1.15MM, 1.27P CASE 760AB

ISSUE D

1.30


**DATE 22 MAY 2024** 





#### NOTES:

- DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 2018.
- CONTROLLING DIMENSION: MILLIMETERS.
- 3. DIMENSIONS D AND E DO NOT INCLUDE MOLD FLASH, PROTRUSIONS, OR BURRS. MOLD FLASH PROTRUSIONS OR GATE BURRS SHALL NOT EXCEED 0.150mm PER SIDE.
- 4. DIMENSIONS D AND E ARE DETERMINED AT THE OUTERMOST EXTREMES OF THE PLASTIC BODY.



D4

(D8)

| - | 1.61                               |
|---|------------------------------------|
| 1 | 0.70                               |
|   | ↑                                  |
|   |                                    |
| , | 1.15                               |
|   |                                    |
|   |                                    |
|   | 0.70 -   -   1.27   -              |
|   | RECOMMENDED LAND PATTERN           |
|   | *FOR ADDITIONAL INFORMATION ON OUR |
|   | PB-FREE STRATEGY AND SOLDERING     |
|   | I B THEE OH WILLIAM GOLDLINIA      |

\*FOR ADDITIONAL INFORMATION ON OUR PB-FREE STRATEGY AND SOLDERING DETAILS, PLEASE DOWNLOAD THE ONSEMI SOLDERING AND MOUNTING TECHNIQUES REFERENCE MANUAL, SOLDERRM/D.

# GENERIC MARKING DIAGRAM\*

**BOTTOM VIEW** 

D5

D6 (D7)

XXXXXX XXXXXX AWLYW XXXXXX = Specific Device Code A = Assembly Location

WL = Wafer Lot Y = Year W = Work Week

\*This information is generic. Please refer to device data sheet for actual part marking. Some products may not follow the Generic Marking.

| DIM         MIN         NOM         MAX           A         1.10         1.20         1.30           A1         0.00         0.08         0.15           A2         1.10         1.15         1.20           A3         0.25 BSC         0.50           b         0.40         0.45         0.50           b2         3.80         4.10         4.40           b4         0.45         0.55         0.65           c         0.19         0.22         0.25           c2         0.19         0.22         0.25           D         4.15 BSC         0.20         0.25           D1         3.80         4.00         4.20           D2         3.00         3.10         3.20           D3         0.30         0.40         0.50           D4         0.90         1.00         1.10           D5         0.70         0.80         0.90           D6         0.55         0.65         0.75           D7         0.31 REF           D8         0.40 REF           E         4.90 BSC           E1         4.85         4.95 <td< th=""><th colspan="6">MILLIMETER</th></td<> | MILLIMETER      |          |          |      |  |  |
|---|-----------------|----------|----------|------|--|--|
| A1       0.00       0.08       0.15         A2       1.10       1.15       1.20         A3       0.25 BSC         b       0.40       0.45       0.50         b2       3.80       4.10       4.40         b4       0.45       0.55       0.65         c       0.19       0.22       0.25         c2       0.19       0.22       0.25         D       4.15 BSC         D1       3.80       4.00       4.20         D2       3.00       3.10       3.20         D3       0.30       0.40       0.50         D4       0.90       1.00       1.10         D5       0.70       0.80       0.90         D6       0.55       0.65       0.75         D7       0.31 REF         D8       0.40 REF         E       4.90 BSC         E1       4.85       4.95       5.05         E2       3.10       3.20       3.30         E3       0.00       0.10       0.20         E4       2.00       2.10       2.20         e       1.27 BSC         e/2<   | DIM MIN NOM MAX |          |          |      |  |  |
| A2       1.10       1.15       1.20         A3       0.25 BSC         b       0.40       0.45       0.50         b2       3.80       4.10       4.40         b4       0.45       0.55       0.65         c       0.19       0.22       0.25         c2       0.19       0.22       0.25         D1       3.80       4.00       4.20         D2       3.00       3.10       3.20         D3       0.30       0.40       0.50         D4       0.90       1.00       1.10         D5       0.70       0.80       0.90         D6       0.55       0.65       0.75         D7       0.31 REF         D8       0.40 REF         E       4.90 BSC         E1       4.85       4.95       5.05         E2       3.10       3.20       3.30         E3       0.00       0.10       0.20         E4       2.00       2.10       2.20         e       1.27 BSC         e/2       0.635 BSC         e1       0.40 REF         H       6.00  | Α               | 1.10     | 1.20     | 1.30 |  |  |
| A3  | A1              | 0.00     | 0.08     | 0.15 |  |  |
| b         0.40         0.45         0.50           b2         3.80         4.10         4.40           b4         0.45         0.55         0.65           c         0.19         0.22         0.25           c2         0.19         0.22         0.25           D         4.15 BSC           D1         3.80         4.00         4.20           D2         3.00         3.10         3.20           D3         0.30         0.40         0.50           D4         0.90         1.00         1.10           D5         0.70         0.80         0.90           D6         0.55         0.65         0.75           D7         0.31 REF           B8         0.40 REF           E         4.90 BSC           E1         4.85         4.95         5.05           E2         3.10         3.20         3.30           E3         0.00         0.10         0.20           E4         2.00         2.10         2.20           e         1.27 BSC           e/2         0.635 BSC           e1         0.40 REF  | A2              | 1.10     | 1.15     | 1.20 |  |  |
| b2       3.80       4.10       4.40         b4       0.45       0.55       0.65         c       0.19       0.22       0.25         c2       0.19       0.22       0.25         D       4.15 BSC         D1       3.80       4.00       4.20         D2       3.00       3.10       3.20         D3       0.30       0.40       0.50         D4       0.90       1.00       1.10         D5       0.70       0.80       0.90         D6       0.55       0.65       0.75         D7       0.31 REF         D8       0.40 REF         E       4.90 BSC         E1       4.85       4.95       5.05         E2       3.10       3.20       3.30         E3       0.00       0.10       0.20         E4       2.00       2.10       2.20         e       1.27 BSC         e/2       0.635 BSC         e1       0.40 REF         H       6.00       6.15       6.30         L       0.50       0.70       0.90         L1       0.80       0   | Α3              | (        | ).25 BSC |      |  |  |
| b4         0.45         0.55         0.65           c         0.19         0.22         0.25           c2         0.19         0.22         0.25           D         4.15 BSC           D1         3.80         4.00         4.20           D2         3.00         3.10         3.20           D3         0.30         0.40         0.50           D4         0.90         1.00         1.10           D5         0.70         0.80         0.90           D6         0.55         0.65         0.75           D7         0.31 REF           D8         0.40 REF           E         4.90 BSC           E1         4.85         4.95         5.05           E2         3.10         3.20         3.30           E3         0.00         0.10         0.20           E4         2.00         2.10         2.20           e         1.27 BSC           e/2         0.635 BSC           e1         0.40 REF           H         6.00         6.15         6.30           L         0.50         0.70         0.90   | b               | 0.40     | 0.45     | 0.50 |  |  |
| C         0.19         0.22         0.25           c2         0.19         0.22         0.25           D         4.15 BSC           D1         3.80         4.00         4.20           D2         3.00         3.10         3.20           D3         0.30         0.40         0.50           D4         0.90         1.00         1.10           D5         0.70         0.80         0.90           D6         0.55         0.65         0.75           D7         0.31 REF           D8         0.40 REF           E         4.90 BSC           E1         4.85         4.95         5.05           E2         3.10         3.20         3.30           E3         0.00         0.10         0.20           E4         2.00         2.10         2.20           e         1.27 BSC           e/2         0.635 BSC           e1         0.40 REF           H         6.00         6.15         6.30           L         0.50         0.70         0.90           L1         0.80         0.90         1.00   | b2              | 3.80     | 4.10     | 4.40 |  |  |
| C2         0.19         0.22         0.25           D         4.15 BSC           D1         3.80         4.00         4.20           D2         3.00         3.10         3.20           D3         0.30         0.40         0.50           D4         0.90         1.00         1.10           D5         0.70         0.80         0.90           D6         0.55         0.65         0.75           D7         0.31 REF           D8         0.40 REF           E         4.90 BSC           E1         4.85         4.95         5.05           E2         3.10         3.20         3.30           E3         0.00         0.10         0.20           E4         2.00         2.10         2.20           e         1.27 BSC           e/2         0.635 BSC           e1         0.40 REF           H         6.00         6.15         6.30           L         0.50         0.70         0.90           L1         0.80         0.90         1.00           L2         1.10 REF         1.10 REF   | b4              |          | 0.55     |      |  |  |
| D         4.15 BSC           D1         3.80         4.00         4.20           D2         3.00         3.10         3.20           D3         0.30         0.40         0.50           D4         0.90         1.00         1.10           D5         0.70         0.80         0.90           D6         0.55         0.65         0.75           D7         0.31 REF           D8         0.40 REF           E         4.90 BSC           E1         4.85         4.95         5.05           E2         3.10         3.20         3.30           E3         0.00         0.10         0.20           E4         2.00         2.10         2.20           e         1.27 BSC           e/2         0.635 BSC           e1         0.40 REF           H         6.00         6.15         6.30           L         0.50         0.70         0.90           L1         0.80         0.90         1.00           L2         1.10 REF  | C               | 0.19     |          | 0.25 |  |  |
| D1         3.80         4.00         4.20           D2         3.00         3.10         3.20           D3         0.30         0.40         0.50           D4         0.90         1.00         1.10           D5         0.70         0.80         0.90           D6         0.55         0.65         0.75           D7         0.31 REF           D8         0.40 REF           E         4.90 BSC           E1         4.85         4.95         5.05           E2         3.10         3.20         3.30           E3         0.00         0.10         0.20           E4         2.00         2.10         2.20           e         1.27 BSC           e/2         0.635 BSC           e1         0.40 REF           H         6.00         6.15         6.30           L         0.50         0.70         0.90           L1         0.80         0.90         1.00           L2         1.10 REF   |                 |          |          |      |  |  |
| D2         3.00         3.10         3.20           D3         0.30         0.40         0.50           D4         0.90         1.00         1.10           D5         0.70         0.80         0.90           D6         0.55         0.65         0.75           D7         0.31 REF           D8         0.40 REF           E         4.90 BSC           E1         4.85         4.95         5.05           E2         3.10         3.20         3.30           E3         0.00         0.10         0.20           E4         2.00         2.10         2.20           e         1.27 BSC           e/2         0.635 BSC           e1         0.40 REF           H         6.00         6.15         6.30           L         0.50         0.70         0.90           L1         0.80         0.90         1.00           L2         1.10 REF   |                 | 4        | 4.15 BS  | 2    |  |  |
| D3         0.30         0.40         0.50           D4         0.90         1.00         1.10           D5         0.70         0.80         0.90           D6         0.55         0.65         0.75           D7         0.31 REF           D8         0.40 REF           E         4.90 BSC           E1         4.85         4.95         5.05           E2         3.10         3.20         3.30           E3         0.00         0.10         0.20           E4         2.00         2.10         2.20           e         1.27 BSC           e/2         0.635 BSC           e1         0.40 REF           H         6.00         6.15         6.30           L         0.50         0.70         0.90           L1         0.80         0.90         1.00           L2         1.10 REF   | D1              | 3.80     | 4.00     | 4.20 |  |  |
| D4         0.90         1.00         1.10           D5         0.70         0.80         0.90           D6         0.55         0.65         0.75           D7         0.31 REF           D8         0.40 REF           E         4.90 BSC           E1         4.85         4.95         5.05           E2         3.10         3.20         3.30           E3         0.00         0.10         0.20           E4         2.00         2.10         2.20           e         1.27 BSC           e/2         0.635 BSC           e1         0.40 REF           H         6.00         6.15         6.30           L         0.50         0.70         0.90           L1         0.80         0.90         1.00           L2         1.10 REF   | D2              | 3.00     | 3.10     | 3.20 |  |  |
| D5         0.70         0.80         0.90           D6         0.55         0.65         0.75           D7         0.31 REF           D8         0.40 REF           E         4.90 BSC           E1         4.85         4.95         5.05           E2         3.10         3.20         3.30           E3         0.00         0.10         0.20           E4         2.00         2.10         2.20           e         1.27 BSC           e/2         0.635 BSC           e1         0.40 REF           H         6.00         6.15         6.30           L         0.50         0.70         0.90           L1         0.80         0.90         1.00           L2         1.10 REF   | D3              | 0.30     | 0.40     | 0.50 |  |  |
| D6         0.55         0.65         0.75           D7         0.31 REF           D8         0.40 REF           E         4.90 BSC           E1         4.85         4.95         5.05           E2         3.10         3.20         3.30           E3         0.00         0.10         0.20           E4         2.00         2.10         2.20           e         1.27 BSC           e/2         0.635 BSC           e1         0.40 REF           H         6.00         6.15         6.30           L         0.50         0.70         0.90           L1         0.80         0.90         1.00           L2         1.10 REF   | D4              | 0.90     | 1.00     | 1.10 |  |  |
| D7       0.31 REF         D8       0.40 REF         E       4.90 BSC         E1       4.85       4.95       5.05         E2       3.10       3.20       3.30         E3       0.00       0.10       0.20         E4       2.00       2.10       2.20         e       1.27 BSC         e/2       0.635 BSC         e1       0.40 REF         H       6.00       6.15       6.30         L       0.50       0.70       0.90         L1       0.80       0.90       1.00         L2       1.10 REF   | D5              | 0.70     | 0.80     | 0.90 |  |  |
| D8       0.40 REF         E       4.90 BSC         E1       4.85       4.95       5.05         E2       3.10       3.20       3.30         E3       0.00       0.10       0.20         E4       2.00       2.10       2.20         e       1.27 BSC         e/2       0.635 BSC         e1       0.40 REF         H       6.00       6.15       6.30         L       0.50       0.70       0.90         L1       0.80       0.90       1.00         L2       1.10 REF   | D6              | 0.55     | 0.65     | 0.75 |  |  |
| E   | D7              |          | 0.31 REI | F    |  |  |
| E1     4.85     4.95     5.05       E2     3.10     3.20     3.30       E3     0.00     0.10     0.20       E4     2.00     2.10     2.20       e     1.27 BSC       e/2     0.635 BSC       e1     0.40 REF       H     6.00     6.15     6.30       L     0.50     0.70     0.90       L1     0.80     0.90     1.00       L2     1.10 REF  | D8              |          | 0.40 REI | F    |  |  |
| E2       3.10       3.20       3.30         E3       0.00       0.10       0.20         E4       2.00       2.10       2.20         e       1.27 BSC         e/2       0.635 BSC         e1       0.40 REF         H       6.00       6.15       6.30         L       0.50       0.70       0.90         L1       0.80       0.90       1.00         L2       1.10 REF  |                 | 4        | 4.90 BS  | 0    |  |  |
| E3     0.00     0.10     0.20       E4     2.00     2.10     2.20       e     1.27 BSC       e/2     0.635 BSC       e1     0.40 REF       H     6.00     6.15     6.30       L     0.50     0.70     0.90       L1     0.80     0.90     1.00       L2     1.10 REF  |                 | 4.85     | 4.95     | 5.05 |  |  |
| E4 2.00 2.10 2.20 e 1.27 BSC e/2 0.635 BSC e1 0.40 REF H 6.00 6.15 6.30 L 0.50 0.70 0.90 L1 0.80 0.90 1.00 L2 1.10 REF  | E2              | 3.10     | 3.20     | 3.30 |  |  |
| e     1.27 BSC       e/2     0.635 BSC       e1     0.40 REF       H     6.00     6.15     6.30       L     0.50     0.70     0.90       L1     0.80     0.90     1.00       L2     1.10 REF  | E3              | 0.00     |          |      |  |  |
| e     1.27 BSC       e/2     0.635 BSC       e1     0.40 REF       H     6.00     6.15     6.30       L     0.50     0.70     0.90       L1     0.80     0.90     1.00       L2     1.10 REF  | E4              |          |          | 2.20 |  |  |
| e1     0.40 REF       H     6.00     6.15     6.30       L     0.50     0.70     0.90       L1     0.80     0.90     1.00       L2     1.10 REF   | е               | 1.27 BSC |          |      |  |  |
| H 6.00 6.15 6.30<br>L 0.50 0.70 0.90<br>L1 0.80 0.90 1.00<br>L2 1.10 REF  | e/2             |          |          |      |  |  |
| L 0.50 0.70 0.90<br>L1 0.80 0.90 1.00<br>L2 1.10 REF  |                 | 0.40 REF |          |      |  |  |
| L1 0.80 0.90 1.00<br>L2 1.10 REF  |                 |          |          |      |  |  |
| L2 1.10 REF   | L               |          |          |      |  |  |
| L2       1.10 REF         Θ       0°       4°       8°  | L1              |          |          |      |  |  |
| Θ 0° 4° 8°  |                 | 1.10 REF |          |      |  |  |
|   | θ               | 0°       | 4°       | 8°   |  |  |

# DOCUMENT NUMBER: 98AON82777G Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red. DESCRIPTION: LFPAK4 4.90x4.15x1.15MM, 1.27P PAGE 1 OF 1

onsemi and ONSEMI are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

onsemi, Onsemi, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at <a href="www.onsemi.com/site/pdf/Patent-Marking.pdf">www.onsemi.com/site/pdf/Patent-Marking.pdf</a>. Onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA class 3 medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase

#### ADDITIONAL INFORMATION

**TECHNICAL PUBLICATIONS:** 

 $\textbf{Technical Library:} \ \underline{www.onsemi.com/design/resources/technical-documentation}$ 

onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at

www.onsemi.com/support/sales