

VC2010 High-Performance Spindle/VCM Control

Features

VCM Actuator Predriver

- Transconductance amplifier with selectable class B or AB mode
- 14-bit DAC for actuator current control
- Regulated 3-stage retract on voltage fault or command
- Programmable on-chip transconductance compensation reduces external component count

Spindle Control

- Motor inductance sense mode for determination of motor start position
- Microprocessor controlled ramp-to-start speed in start mode
- Sinusoidal current mode or 6-state commutation in run mode
- Programmable wave shape for optimized acoustic performance
- Transconductance configuration in run mode, using PWM for efficiency
- Peak current-limit control in start mode, using constant off-time method
- 10-bit DAC with 4-step gain ranging
- Fast restart from partial spindown, using phase frequency comparison of BEMF
- Automatic spindle dynamic brake at programmable RPM after retract

Serial Port Interface

- 30 MHz read/write serial port
- 3.3 V TTL compatible digital I/O, 5 V CMOS input tolerant

Voltage Monitor, System Reset, and Auxiliary Supplies

- 5 V, 12 V, and 3.3 V undervoltage fault comparators
- Power-on reset signal output
- 3.3 V regulator with voltage margin control and current limit
- Resistor adjustable negative voltage regulator for MR preamplifiers
- Programmable output voltage switching and linear regulators with undervoltage monitoring

Other Features

- 12-bit DAC to drive external microactuator driver
- 10-bit ADC to digitize selected internal and external signals
- Special diagnostic features for observation of on-chip signals
- Supports 3-stage constant voltage retract

Pin Information





Figure 1. VC2010 Pin Diagram

Block Diagram



2537 (F)

Figure 2. VC2010 Block Diagram

For additional information, contact your Agere Systems Account Manager or the following:

INTERNET: <http://www.agere.com>

E-MAIL: docmaster@agere.com

N. AMERICA: Agere Systems Inc., 555 Union Boulevard, Room 30L-15P-BA, Allentown, PA 18109-3286

1-800-372-2447, FAX 610-712-4106 (In CANADA: 1-800-553-2448, FAX 610-712-4106)

ASIA: Agere Systems Hong Kong Ltd., Suites 3201 & 3210-12, 32/F, Tower 2, The Gateway, Harbour City, Kowloon

Tel. (852) 3129-2000, FAX (852) 3129-2020

CHINA: (86) 21-5047-1212 (Shanghai), (86) 10-6522-5566 (Beijing), (86) 755-695-7224 (Shenzhen)

JAPAN: (81) 3-5421-1600 (Tokyo), KOREA: (82) 2-767-1850 (Seoul), SINGAPORE: (65) 778-8833, TAIWAN: (886) 2-2725-5858 (Taipei)

EUROPE: Tel. (44) 7000 624624, FAX (44) 1344 488 045

Agere Systems Inc. reserves the right to make changes to the product(s) or information contained herein without notice. No liability is assumed as a result of their use or application.